

Elma Clean Box

Ultrasonic Cleaning Unit

Elma order nos

Elma Clean Box with basket and cover (230 V)	100 3174
Elma Clean Box with basket and cover (120 V)	103 4843
Elma Clean Box with basket and cover (100 V)	103 4844
Elma Clean Box with basket, cover, wall bracket, forceps, 2 cleaning cups (230V)	229 010 0000



Pictured Elma Clean Box

A good way to start professional ultrasonic cleaning.

Product features:

- Suitable for the cleaning of jewellery, spectacles, prosthesis and instruments
- The cleaning beakers allow the hygienic cleaning of different cleaning items at the same time. (e.g. prosthesis, drills, cutters)
- In addition, it is possible to use a different cleaning media in each of the beakers
- Easy and comfortable to operate
- Pre-programmed cleaning time
- Good visible LED-display
- Practicable: the translucent lid can also be used as basket holder (drip drying)

Delivery includes/inclusive of:

Ultrasonic cleaning unit, cleaning basket, lid, two cleaning beakers, pincette, wall bracket

Technical data

Ultrasonic frequency (kHz)	46	Inner dimensions of basket w/d/h (mm)	178 / 80 / 47
Power requirement (VA)	40	Inner dimensions of basket w/d/h (inch)	7.0 / 3.15 / 1.85
Voltage (Vac)	100 to 240V	Mesh size basket (mm) / (inch)	6 / 0.25
Power frequency (Hz)	50 / 60	Weight (ca. kg / lbs)	1,0 / 2.21
Outer dimensions of unit w/d/h (mm)	212 / 122 / 130	Material tank	Stainless steel
Outer dimensions of unit w/d/h (inch)	8.35 / 4.80 / 5.12	Material casing	PC-ABS
Inner dimensions of basket w/d/h (mm)	194 / 84 / 60	Material lid	PET
Inner dimensions of basket w/d/h (inch)	7.64 / 3.31 / 2.36	CE-compliant	√
Tank capacity (litres / gal.)	0.9 / 0.24		



www.ert.pt
info@ert.pt
Telf. 217 142 066 - Fax. 217 145 674

Rua Soeiro Pereira Gomes, Lote 5, Cave Drt.
2845-387 Amora Portugal

Subject to technical and optical changes reserved Elma_ch_01/07