

Flame Photometers

- Industrial version supplied with Na, K, Li, Ba & Ca filters
- Clinical version supplied with Na, K & Li filters
- Low temperature, single channel
- Electronic ignition



- Flame failure safety system
- Operates on propane, butane, natural gas or L.P.G. supplies
- Fine & coarse sensitivity controls

The Jenway Models PFP7 and PFP7/C are low temperature, single channel flame photometers, designed for the routine determinations of Sodium (Na), Potassium (K), Calcium (Ca), Barium (Ba) and Lithium (Li).

Both versions are fitted with automatic flame failure detection for user safety, making them ideal for use in clinical, industrial or educational applications.



The Model PFP7/C is specifically designed for use in clinical applications. The in-built lineariser circuitry enables readings of both Na and K, at the normal clinical serum concentrations, to be displayed directly in mmol/l. Serum samples must be diluted 200:1 or 100:1 prior to presentation to the flame photometer. Jenway are able to offer the Series 7 Diluter to enable this to be carried out efficiently and accurately.

Technical Specifications

Model	PFP7 (Industrial)	PFP7/C (Clinical)
Ranges	0-199.9	120-160mmol/l Na (linearised) 0-10.0mmol/lK
Limits of Detection	Na ≤ 0.2ppm K ≤ 0.2ppm Li ≤ 0.25ppm Ca ≤ 15ppm Ba ≤ 30ppm	– – Li ≤ 0.25ppm Ca ≤ 15ppm Ba ≤ 30ppm
Reproducibility	≤1% Coefficient of Variation for 20 consecutive samples using 10ppm Na set to read 50	
Linearity	Better than 2% when concentration of 3ppm Na/K and 5ppm Li are set to read 100	
Specificity	Interference from Na/K and Li equal in concentration to test element will be <0.5%	
Recorder Output Services	Nominal 1.00V for a reading of 100.0 Electrical: 90-125V or 190-250V @ 50/60Hz Air: moisture and oil free 6 litre/minute @ 1kg/cm ² (14psi) Fuel: Propane, Butane, Natural Gas or L.P.G.	
Size	420 x 360 x 300mm	
Weight	8kg	

Order Codes

- 500 701** Model PFP7 supplied with Na, K, Li, Ba & Ca filters, connecting hoses and clips, compressor plug, drain trap, fuses and operating/service instructions. For use on 230V 50Hz.
- 500 731** Model PFP7 supplied with Na, K, Li, Ba & Ca filters, connecting hoses and clips, compressor plug, drain trap, fuses and operating/service instructions. For use on 110V 60Hz.
- 500 801** Model PFP7/C supplied with Na, K & Li filters, connecting hoses and clips, compressor plug, drain trap, fuses and operating/service instructions. For use on 230V 50Hz.
- 500 831** Model PFP7/C supplied with Na, K & Li filters, connecting hoses and clips, compressor plug, drain trap, fuses and operating/service instructions. For use on 110V 60Hz.



Jenway
Gransmore Green
Felsted, Dunmow
Essex, CM6 3LB, ENGLAND
Tel: +44 (0)1371 820122
Fax: +44 (0)1371 821083
e-mail: sales@jenway.com
www.jenway.com

Techne Inc.
3 Terri Lane
Suite 10
Burlington
NJ 08016 USA
Tel: 609-589-2560
Fax: 609-589-2571
Toll free: 800 225-9243
www.techneusa.com

Jenway Middle East Overseas Corp.
PO Box 27842
Engomi 2433
Nicosia Cyprus
Tel: 357 22 660423
Fax: 357 22 660424
e-mail: sales@jenwayme.com

Bibby Scientific (Asia) Ltd
Room 607, Yen Sheng Centre
64 Hoi Yuen Road, Kwun Tong
Kowloon, Hong Kong
Tel: 852 3583 1581
Fax: 852 3583 1580
e-mail: bibby@bibby-scientificasia.com
www.bibby-scientificasia.com

Accessories

Please note: These products will only operate with the correct type of air compressor and gas regulator, as specified.

- 535 001** Air compressor (220V/50Hz)
535 002 Air compressor (110V/60Hz)
037 001 Series 7 Diluter (230V/50Hz)
037 002 Series 7 Diluter (110V/60Hz)
500 176 Water separator (small)
500 177 Water separator (large)
500 134 Dust cover
500 172 Minor spares kit
500 173 Major spares kit
500 178 Butane regulator
500 179 Propane regulator
500 180 Natural gas regulator
025 016 Cleaning solution

Clinical Standards (500ml)

- 025 008** 1.00mmol/l Li
025 004 100mmol/l Na/K
025 006 140mmol/l Na / 5mmol/l K
025 007 120mmol/l Na / 2mmol/l K
025 005 160mmol/l Na / 8mmol/l K
025 027 160mmol/l Na / 80mmol/l K

Industrial Standards (500ml)

- 025 023** 1000ppm K
025 024 1000ppm Li
025 025 3000ppm Ba
025 021 1000ppm Na
025 009 1000ppm Ca