




UltraSlim UV transilluminator

As Small As it can!



-  **Focus on mini-gel: 150*80mm viewing**
-  **High Performance: Sensitivity > 1ng**
-  **Small and Economic: Smaller and cheaper**



Dimension	247X132X48.5 mm
Wavelength	302 nm
Weight	1.4 Kg
Gel Size	125X60 mm
Power	12V, 1.5A



www.ert.pt

info@ert.pt

Tel. 217 142 066 - Fax. 217 145 674

Rua Soeiro Pereira Gomes, Lote 5, Cave Drt.
2845-387 Amora Portugal

 **MAESTROGEN**

www.maestrogen.com

info@maestrogen.com

