

CLIMACELL

with forced air convection, cooling
and controlled humidity



The CLIMACELL series was specially developed for applications, in which as far as possible exact and reproducible simulation of various environmental conditions is important, e.g. stability testing of components, packaging materials, food or chemicals, germination studies, plant cell or tissue cultures, insect cultures.

Volume:

111, 222, 404, 707 litres

Working temperature:

without humidity 0 °C up to 99.9 °C,
with humidity: 10 °C up to 90.0 °C

Refrigerant: R 134a (without CFC)

Water quality for generating the humidity:

distilled water, drinking water (max. 50 mg Ca/l)

Controlled humidity: 10 %–90 % RH

**Microprocessor controlled humidifying/
/dehumidifying system**

Inner glass door

Interior:

stainless steel, mat. No. 1.4301 (AISI 304)

Laboratory incubators

The high-tech comfort line with multi-functional microprocessor control unit

- 6 adjustable programs
- chip card system for individual program storage
- RS 232 – interface for printer or PC-communication
- delayed heating start and stop function
- acoustic and visual alarm of error state
- time range 0-40 years with 1 min-intervals
- digital safety thermostat
- real time
- programming temperature ramps
- heating sequences
- programme cycles
- adjustable ventilation rate 10 to 100 %



Options

- –9,9 °C with cooled incubators
- interior lighting – a wide offer of various luminary sources
- access ports \varnothing 25, 50, 100 mm
- keyboard lock (prevents the access of unauthorised persons)
- automatic door lock
- left door versions (excluded volume 707 liters)
- timer programmable water protected inner socket
- exposure/stimulating lighting (white/day light) 6 000–13 000 Lx (according to volume) with digitally adjustable light 10–100 %
- exposure illumination in shelves, especially for photo-stability tests (according to ICH Guideline CPNP/ICH279/95)
- potential-free alarm contact
- PT 100 sensor (with indication on a display or PC)
- special software WarmComm
- check of the door opening (microswitch) during the program with the possibility of the record by means of a printer or software
- stainless steel casing of the device

... c o m f o r t l i n e

Technical data		Model	111	222	404	707
Inter dimensions Chamber, stainless steel	volume	l	111	222	404	707
	width	mm	540	540	540	940
	depth	mm	370	520	520	520
	height	mm	530	760	1410	1410
Volume of the steam space		cca l	163	299	524	876
Trays, stainless steel *)	number	max./usual	7/2	10/2	19/2	19/2
Min. distance between trays		mm	70	70	70	70
Storage area	(w x d)	mm	520x338	520x485	520x485	920x485
Number of outer metal doors		No.	1	1	1	2
Number of inner glass doors		No.	1	1	1	2
Admissible weight of trays	together inside the oven per 1 tray	kg	50	70	100	130
		kg	20	30	30	50
Electricity data	max. power consumption	W	2050	2100	3150	3400
Protective system	mains 50/60 Hz	V	230	230	230	230
			IP 20	IP 20	IP 20	IP 20
Temperature data						
Working temperature	from 0 °C	to °C	99,9	99,9	99,9	99,9
Temperature accuracy in space	at 10 °C	± °C	< 0,5	< 0,5	< 1	< 1
	at 37 °C	± °C	< 0,5	< 0,5	< 1	< 1
		± °C	< 0,2	< 0,2	< 0,3	< 0,4
in time		min	24	25	26	27
Heating/up time to 37 °C from the ambient temperature		min	< 21	< 21	< 21	< 21
Cooling/down time from 22 °C to 10 °C		min	< 21	< 21	< 21	< 21
Recovery time after 1 min. door open	at 37 °C	min	4	4	4	4
	at 50 °C	min	4	4	4	4
Relative humidity	range	%	10–90	10–90	10–90	10–90
Heat emission	at 37 °C	W	70	97	123	148
Noise level - complete incubator		dB	46	50	56	58
Outer dimensions (incl. door and handle, and Rollers)	width	max. mm	760	760	1010	1460
	depth	max. mm	640	790	790	790
	height	max. mm	1100R	1330R	1910R	1910R
Weight	netto	cca kg	101	132	230	270
	brutto	cca kg	131	169	270	316


*) Approx. 50 % of the tray area can be filled in a way a uniform air circulation is enabled inside the chamber.

Note: All technical data are related to 22 °C of ambient temperature and ±10 % voltage swing

Changes in the design and make reserved.

Setting operating conditions of temperature and relative humidity and their limitations

cabinet without door lighting



cabinet with door lighting

